

# ZBFM 5/WH,LGS:1-120 - Zack marker strip

0800271

<https://www.phoenixcontact.com/us/products/0800271>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the versions  
ZBM and ZBFM

Zack marker strip, Sheet, white (RAL 9010), labeled, printed horizontally: consecutive numbers 1 ... 120, mounting type: latching, for terminal block width: 5.2 mm, Number of individual labels: 120, text field height: 5 mm, text field width: 4.5 mm

## Commercial data

Item number	0800271
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2123
GTIN	4017918005870
Weight per piece (including packing)	5.236 g
Weight per piece (excluding packing)	5.236 g
Customs tariff number	49119900
Country of origin	PL

## Technical data

### Product properties

Product type	Terminal marker
Pitch	5.2 mm

### Marking

Number of individual labels	120
Number of individual labels per row	12
Printing direction	printed horizontally
Printing	consecutive numbers 1 ... 120
Slot type	flat

### Dimensions

Width	4.55 mm
Height	6.50 mm
Depth	1.60 mm
Pitch	5.2 mm

### Text field

Text field width	4.5 mm
Text field height	5 mm

### Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# ZBFM 5/WH,LGS:1-120 - Zack marker strip



0800271

<https://www.phoenixcontact.com/us/products/0800271>

## Mounting

Mounting type

latching

# ZBFM 5/WH,LGS:1-120 - Zack marker strip



0800271

<https://www.phoenixcontact.com/us/products/0800271>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# ZBFM 5/WH,LGS:1-120 - Zack marker strip



0800271

<https://www.phoenixcontact.com/us/products/0800271>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)