

PMH 0:GROSSBUCHSTABEN N - Wire marking tag



0800433:N

<https://www.phoenixcontact.com/us/products/0800433:N>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, horizontally labeled with the capital letter: Letters, suitable for diameters 1.4 ... 2.5 mm, yellow, mounting type: slide-on

Commercial data

Item number	0800433:N
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG17
Product key	BG222B
GTIN	4017918559373
Weight per piece (including packing)	0.068 g
Weight per piece (excluding packing)	0.06 g
Customs tariff number	49119900
Country of origin	PL

PMH 0:GROSSBUCHSTABEN N - Wire marking tag



0800433:N

<https://www.phoenixcontact.com/us/products/0800433:N>

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Printing	Letters
----------	---------

Dimensions

Width	3.2 mm
Length	4.50 mm

External dimensions

Outside diameter	1.4 mm ... 2.5 mm
------------------	-------------------

Text field

Text field width	3.20 mm
Text field height	2.60 mm

Material specifications

Color	yellow (RAL 1018)
Material	Ethylene-vinyl acetate (EVA)
Flammability rating according to UL 94	V0
Components	free from silicone, halogen, and cadmium

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	slide-on
---------------	----------

PMH 0:GROSSBUCHSTABEN N - Wire marking tag



0800433:N

<https://www.phoenixcontact.com/us/products/0800433:N>

Classifications

ECLASS

ECLASS-13.0

27281102

ETIM

ETIM 9.0

EC001530

UNSPSC

UNSPSC 21.0

39131500

PMH 0:GROSSBUCHSTABEN N - Wire marking tag



0800433:N

<https://www.phoenixcontact.com/us/products/0800433:N>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com