

PMH 0:GROSSBUCHSTABEN X - Wire marking tag



0800433:X

<https://www.phoenixcontact.com/us/products/0800433:X>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, horizontally labeled with the capital letter: Letters, suitable for diameters 1.4 ... 2.5 mm, yellow, mounting type: slide-on

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0800433:X |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BG17 |
| Product key | BG222B |
| GTIN | 4017918559472 |
| Weight per piece (including packing) | 0.072 g |
| Weight per piece (excluding packing) | 0.06 g |
| Customs tariff number | 49119900 |
| Country of origin | PL |

PMH 0:GROSSBUCHSTABEN X - Wire marking tag



0800433:X

<https://www.phoenixcontact.com/us/products/0800433:X>

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

Marking

| | |
|----------|---------|
| Printing | Letters |
|----------|---------|

Dimensions

| | |
|--------|---------|
| Width | 3.2 mm |
| Length | 4.50 mm |

External dimensions

| | |
|------------------|-------------------|
| Outside diameter | 1.4 mm ... 2.5 mm |
|------------------|-------------------|

Text field

| | |
|-------------------|---------|
| Text field width | 3.20 mm |
| Text field height | 2.60 mm |

Material specifications

| | |
|--|--|
| Color | yellow (RAL 1018) |
| Material | Ethylene-vinyl acetate (EVA) |
| Flammability rating according to UL 94 | V0 |
| Components | free from silicone, halogen, and cadmium |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

PMH 0:GROSSBUCHSTABEN X - Wire marking tag



0800433:X

<https://www.phoenixcontact.com/us/products/0800433:X>

Classifications

ECLASS

ECLASS-13.0

27281102

ETIM

ETIM 9.0

EC001530

UNSPSC

UNSPSC 21.0

39131500

PMH 0:GROSSBUCHSTABEN X - Wire marking tag



0800433:X

<https://www.phoenixcontact.com/us/products/0800433:X>

Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | |
|-------------------------------------|--|
|-------------------------------------|--|

| | |
|--|----------------------------|
| | No substance above 0.1 wt% |
|--|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com