

# PMH 2:SYMBOLE L1 - Wire marking tag

0800527:L1

<https://www.phoenixcontact.com/us/products/0800527:L1>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, horizontally labeled with the symbol: Symbols, suitable for diameters 3.0 ... 6.0 mm, yellow, mounting type: slide-on

## Commercial data

Item number	0800527:L1
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG17
Product key	BG222B
GTIN	4017918490805
Weight per piece (including packing)	0.532 g
Weight per piece (excluding packing)	0.447 g
Customs tariff number	49119900
Country of origin	PL

# PMH 2:SYMBOLE L1 - Wire marking tag



0800527:L1

<https://www.phoenixcontact.com/us/products/0800527:L1>

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Printing	Symbols
----------	---------

### Dimensions

Width	4.2 mm
Height	9.5 mm
Length	6.60 mm

### External dimensions

Outside diameter	3 mm ... 6 mm
------------------	---------------

### Text field

Text field width	4.20 mm
Text field height	2.60 mm

### Material specifications

Color	yellow (RAL 1018)
Material	Ethylene-vinyl acetate (EVA)
Flammability rating according to UL 94	V0
Components	free from silicone, halogen, and cadmium

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	slide-on
---------------	----------

# PMH 2:SYMBOLE L1 - Wire marking tag



0800527:L1

<https://www.phoenixcontact.com/us/products/0800527:L1>

## Classifications

### ECLASS

ECLASS-13.0

27281102

### ETIM

ETIM 9.0

EC001530

### UNSPSC

UNSPSC 21.0

39131500

# PMH 2:SYMBOLE L1 - Wire marking tag



0800527:L1

<https://www.phoenixcontact.com/us/products/0800527:L1>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)