

# PMH 3:GROSSBUCHSTABEN X - Wire marking tag



0800556:X

<https://www.phoenixcontact.com/us/products/0800556:X>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, horizontally labeled with the capital letter: Letters, suitable for diameters 5.0 ... 9.0 mm, yellow, mounting type: slide-on

## Commercial data

Item number	0800556:X
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG17
Product key	BG222B
GTIN	4017918491109
Weight per piece (including packing)	560 MGM
Weight per piece (excluding packing)	560 MGM
Customs tariff number	49119900
Country of origin	CZ

# PMH 3:GROSSBUCHSTABEN X - Wire marking tag



0800556:X

<https://www.phoenixcontact.com/us/products/0800556:X>

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Printing	Letters
----------	---------

### Dimensions

Width	4.2 mm
Height	9.5 mm
Length	6.60 mm

### External dimensions

Outside diameter	5 mm ... 9 mm
------------------	---------------

### Text field

Text field width	4.20 mm
Text field height	2.60 mm

### Material specifications

Color	yellow (RAL 1018)
Material	Ethylene-vinyl acetate (EVA)
Flammability rating according to UL 94	V0
Components	free from silicone, halogen, and cadmium

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	slide-on
---------------	----------

# PMH 3:GROSSBUCHSTABEN X - Wire marking tag



0800556:X

<https://www.phoenixcontact.com/us/products/0800556:X>

## Classifications

### ECLASS

ECLASS-13.0

27281102

### UNSPSC

UNSPSC 21.0

39131500

# PMH 3:GROSSBUCHSTABEN X - Wire marking tag



0800556:X

<https://www.phoenixcontact.com/us/products/0800556:X>

## Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)