

# PMH 4:GROSSBUCHSTABEN L - Wire marking tag



0800598:L

<https://www.phoenixcontact.com/us/products/0800598:L>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, horizontally labeled with the capital letter: Letters, suitable for diameters 8.5 ... 12.0 mm, yellow, mounting type: slide-on

## Commercial data

Item number	0800598:L
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG17
Product key	BG222B
GTIN	4017918491246
Weight per piece (including packing)	770 MGM
Weight per piece (excluding packing)	720 MGM
Customs tariff number	49119900
Country of origin	CZ

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Printing	Letters
----------	---------

### Dimensions

Width	6.2 mm
Height	16.5 mm
Length	11.00 mm

### External dimensions

Outside diameter	8.5 mm ... 12 mm
------------------	------------------

### Text field

Text field width	6.20 mm
Text field height	4.00 mm

### Material specifications

Color	yellow (RAL 1018)
Material	Ethylene-vinyl acetate (EVA)
Flammability rating according to UL 94	V0
Components	free from silicone, halogen, and cadmium

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	slide-on
---------------	----------

0800598:L

<https://www.phoenixcontact.com/us/products/0800598:L>

## Classifications

### ECLASS

ECLASS-13.0

27281102

### ETIM

ETIM 9.0

EC001530

### UNSPSC

UNSPSC 21.0

39131500

# PMH 4:GROSSBUCHSTABEN L - Wire marking tag



0800598:L

<https://www.phoenixcontact.com/us/products/0800598:L>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)