

# THERMOMARK-RIBBON 110/50-TC - Ink ribbon



0801384

<https://www.phoenixcontact.com/us/products/0801384>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., length: 50 m, roll length: 50 m, width: 110 mm, color: black

## Commercial data

Item number	0801384
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG02
Product key	BG1223
GTIN	4046356644815
Weight per piece (including packing)	114.2 g
Weight per piece (excluding packing)	108.4 g
Customs tariff number	96121010
Country of origin	FR

# THERMOMARK-RIBBON 110/50-TC - Ink ribbon



0801384

<https://www.phoenixcontact.com/us/products/0801384>

## Technical data

### Product properties

Product type	Ink ribbon
--------------	------------

### Marking

Identification technology	Thermal transfer
---------------------------	------------------

### Dimensions

Width	110 mm
Length	50 m
Length of roll	50 m

### Material specifications

Color	black (RAL 9005)
Material	Polyester

### Environmental and real-life conditions

#### Ambient conditions

Recommended ambient temperature (storage/transport)	5 °C
Recommended humidity (storage/transport)	20 %

# THERMOMARK-RIBBON 110/50-TC - Ink ribbon



0801384

<https://www.phoenixcontact.com/us/products/0801384>

## Classifications

### ECLASS

ECLASS-13.0	19140614
ECLASS-15.0	19140614

### ETIM

ETIM 10.0	EC001694
-----------	----------

### UNSPSC

UNSPSC 21.0	44103100
-------------	----------

# THERMOMARK-RIBBON 110/50-TC - Ink ribbon



0801384

<https://www.phoenixcontact.com/us/products/0801384>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)