

# CES-SRG-BK-4 - Cable sleeve



0801632

<https://www.phoenixcontact.com/us/products/0801632>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable sleeve, small, no. of conductors: 1, type: Round cable, slotted, external cable diameter: 1x 3 mm ... 4 mm, material: NBR, color: black, length: 29.5 mm, width: 19.5 mm, height: 17 mm

## Product description

Slotted cable sleeve

## Commercial data

Item number	0801632
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF67
Product key	AF7CCX
GTIN	4046356674638
Weight per piece (including packing)	8.92 g
Weight per piece (excluding packing)	9.05 g
Customs tariff number	40169997
Country of origin	TW

# CES-SRG-BK-4 - Cable sleeve

0801632


<https://www.phoenixcontact.com/us/products/0801632>

## Technical data

### Product properties

Product type	Cable sleeve
No. of conductors	1

### Dimensions

Dimensional drawing	
Width	19.5 mm
Height	17 mm
Length	29.5 mm

### Material specifications

Material	NBR
----------	-----

### Cable/line

External cable diameter	1x 3 mm ... 4 mm
-------------------------	------------------

### Characteristics

Seal size	small
Design, Format	Round cable
Design, Cable seal	slotted

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-40 °C ... 125 °C (static)


# CES-SRG-BK-4 - Cable sleeve

0801632

<https://www.phoenixcontact.com/us/products/0801632>

## Drawings

Dimensional drawing



Dimensional drawing

# CES-SRG-BK-4 - Cable sleeve



0801632

<https://www.phoenixcontact.com/us/products/0801632>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0801632>

**DNV**

Approval ID: TAE00003VJ

# CES-SRG-BK-4 - Cable sleeve



0801632

<https://www.phoenixcontact.com/us/products/0801632>

## Classifications

### ECLASS

ECLASS-13.0	27144425
ECLASS-15.0	27144425

### ETIM

ETIM 10.0	EC000451
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CES-SRG-BK-4 - Cable sleeve



0801632

<https://www.phoenixcontact.com/us/products/0801632>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)