

# TM-RIBBON 110-WMTB HF WH - Ink ribbon



0802990

<https://www.phoenixcontact.com/us/products/0802990>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, for roll printer for printing product group WMTB HF..., length: 300 m, roll length: 300 m, width: 110 mm

## Commercial data

Item number	0802990
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG02
Product key	BG1223
GTIN	4046356891035
Weight per piece (including packing)	459.9 g
Weight per piece (excluding packing)	428.5 g
Customs tariff number	96121010
Country of origin	DE

# TM-RIBBON 110-WMTB HF WH - Ink ribbon



0802990

<https://www.phoenixcontact.com/us/products/0802990>

## Technical data

### Product properties

Product type	Ink ribbon
--------------	------------

### Marking

Identification technology	Thermal transfer
---------------------------	------------------

### Dimensions

Width	110 mm
Length	300 m
Length of roll	300 m

### Material specifications

Color	white (RAL 9010)
Base element material	Polyester

### Environmental and real-life conditions

#### Ambient conditions

Recommended ambient temperature (storage/transport)	5 °C
Recommended humidity (storage/transport)	30 %

# TM-RIBBON 110-WMTB HF WH - Ink ribbon



0802990

<https://www.phoenixcontact.com/us/products/0802990>

## Classifications

### ECLASS

ECLASS-13.0	19140614
ECLASS-15.0	19140614

### ETIM

ETIM 10.0	EC001694
-----------	----------

### UNSPSC

UNSPSC 21.0	44103100
-------------	----------

# TM-RIBBON 110-WMTB HF WH - Ink ribbon



0802990

<https://www.phoenixcontact.com/us/products/0802990>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)