

THERMOFOX SET - Thermal transfer printer set



0803986

<https://www.phoenixcontact.com/us/products/0803986>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Portable thermal transfer printer for materials off the roll, with accessories (adapter, battery, USB cable, MM-EMLF (18XE) WH/BK and EMLC (18xE) WH/BK materials) in hard-shell case

Your advantages

- Maintenance-free operation with proven thermal transfer printer technology
- Printing of self-adhesive, non-sticky labels and shrink sleeves
- The THERMOFOX prints materials in cassette format, which contain the material to be marked and the appropriate ink ribbon.
- 8 different barcodes and over 300 symbols can be integrated.
- Intuitive user guidance thanks to a well-structured menu and direct input keys
- Easy to control with the PROJECT COMPLETE software

Commercial data

Item number	0803986
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG01
Product key	BG1222
GTIN	4055626212609
Weight per piece (including packing)	2,259 g
Weight per piece (excluding packing)	2,259 g
Customs tariff number	84433210
Country of origin	CN

THERMOFOX SET - Thermal transfer printer set



0803986

<https://www.phoenixcontact.com/us/products/0803986>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Marking system
--------------	----------------

Marking

Identification technology	Thermal transfer
---------------------------	------------------

Device properties

Print width	24 mm
Print resolution	300 dpi
Operating system	MS Windows 7, MS Windows 8.1, MS Windows 10

Dimensions

Width	98 mm
Height	69 mm
Length	230 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 40 °C
---------------------------------	----------------

THERMOFOX SET - Thermal transfer printer set



0803986

<https://www.phoenixcontact.com/us/products/0803986>

Classifications

UNSPSC

UNSPSC 21.0	43212108
-------------	----------

THERMOFOX SET - Thermal transfer printer set



0803986

<https://www.phoenixcontact.com/us/products/0803986>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-10 An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
--	--

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com