

SK 7,5/3,8:FORTL.ZAHLEN 31-40 - Marker for terminal blocks



0804455:0031

<https://www.phoenixcontact.com/us/products/0804455:0031>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker card, self-adhesive, labeled with the consecutive numbers: 31 ... 40, 10-section marker strips with 12 identical decades, white, for terminal block width: 7.5 mm, mounting type: adhesive



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0804455:0031 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG05 |
| Product key | BG2123 |
| GTIN | 4017918499198 |
| Weight per piece (including packing) | 1.55 g |
| Weight per piece (excluding packing) | 1.211 g |
| Customs tariff number | 49119900 |
| Country of origin | DE |

SK 7,5/3,8:FORTL.ZAHLEN 31-40 - Marker for terminal blocks



0804455:0031

<https://www.phoenixcontact.com/us/products/0804455:0031>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Terminal marker |
| Pitch | 7.5 mm |

Marking

| | |
|----------|-----------|
| Printing | 31 ... 40 |
|----------|-----------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

Material specifications

| | |
|-----------------------|------------------|
| Color | white (RAL 9010) |
| Material | Polyester |
| Base element material | Polyester |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Dimensions

| | |
|--------|--------|
| Width | 7.5 mm |
| Height | 3.8 mm |
| Pitch | 7.5 mm |

Text field

| | |
|-------------------|---------|
| Text field width | 7.50 mm |
| Text field height | 3.80 mm |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

SK 7,5/3,8:FORTL.ZAHLEN 31-40 - Marker for terminal blocks



0804455:0031

<https://www.phoenixcontact.com/us/products/0804455:0031>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

SK 7,5/3,8:FORTL.ZAHLEN 31-40 - Marker for terminal blocks



0804455:0031

<https://www.phoenixcontact.com/us/products/0804455:0031>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com