

# PATG 8/23 - Conductor marker carrier



0808053

<https://www.phoenixcontact.com/us/products/0808053>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Conductor marker carrier, unmarked, cable diameter range: 30 ... 35 mm, mounting type: slide-on, text field height: 4 mm, text field width: 23 mm



## Your advantages

- The corresponding UC-WMT ..., US-WMT ..., and EMT ... insert labels are used for marking
- These conductor marking systems consist of marker carriers and insert labels
- The PATG ... collar is a captive marker carrier
- Can be used to mark conductors with a diameter of 0.6 mm ... 50 mm

## Commercial data

Item number	0808053
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BG12
Product key	BG221A
GTIN	4017918168926
Weight per piece (including packing)	3.17 g
Weight per piece (excluding packing)	3.15 g
Customs tariff number	39269097
Country of origin	DE

0808053

<https://www.phoenixcontact.com/us/products/0808053>

## Technical data

### Product properties

Product type	Marker carriers
--------------	-----------------

### Dimensions

Width	23 mm
Height	50 mm
Depth	21.8 mm

### Text field

Text field width	23 mm
Text field height	4 mm

### Material specifications

RoHS compliant	yes
Color	transparent
Material	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

### Cable/line

External cable diameter	30 mm ... 35 mm
-------------------------	-----------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

### Mounting

Mounting type	slide-on
---------------	----------

# PATG 8/23 - Conductor marker carrier



0808053

<https://www.phoenixcontact.com/us/products/0808053>

## Classifications

### ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

### ETIM

ETIM 10.0	EC002248
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# PATG 8/23 - Conductor marker carrier



0808053

<https://www.phoenixcontact.com/us/products/0808053>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.009 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)