

PMH 0:(100X0-9) - Wire marking tag



0808419

<https://www.phoenixcontact.com/us/products/0808419>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, yellow (RAL 1018), cable diameter range: 1.4 ... 2.5 mm, horizontal: Numbers, mounting type: slide-on, text field height: 2.6 mm, text field width: 3.2 mm

Commercial data

Item number	0808419
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BG222B
GTIN	4017918170028
Weight per piece (including packing)	65.3 g
Weight per piece (excluding packing)	58.5 g
Country of origin	DE

PMH 0:(100X0-9) - Wire marking tag



0808419

<https://www.phoenixcontact.com/us/products/0808419>

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Printing direction	horizontal
Printing	Numbers

Dimensions

Width	3.2 mm
Length	4.5 mm

Text field

Text field width	3.2 mm
Text field height	2.6 mm

Material specifications

Color	yellow (RAL 1018)
Material	Ethylene-vinyl acetate (EVA)
Flammability rating according to UL 94	V0
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	1.4 mm ... 2.5 mm
-------------------------	-------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-45 °C ... 70 °C
---------------------------------	------------------

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	slide-on
---------------	----------

PMH 0:(100X0-9) - Wire marking tag



0808419

<https://www.phoenixcontact.com/us/products/0808419>

Classifications

ECLASS

ECLASS-13.0

27281102

UNSPSC

UNSPSC 21.0

39131500

PMH 0:(100X0-9) - Wire marking tag



0808419

<https://www.phoenixcontact.com/us/products/0808419>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com