

ZBFM 5/OG:UNBEDRUCKT - Flat zack marker sheet




0807180

<https://www.phoenixcontact.com/us/products/0807180>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Flat zack marker sheet, Sheet, orange (RAL 2003), unmarked, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: latching, for terminal block width: 5.2 mm, Number of individual labels: 120



Commercial data

Item number	0807180
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG05
Product key	BG2113
GTIN	4017918157548
Weight per piece (including packing)	6.211 g
Weight per piece (excluding packing)	5.211 g
Customs tariff number	39269097
Country of origin	DE

0807180

<https://www.phoenixcontact.com/us/products/0807180>

Technical data

Product properties

Product type	Terminal marker
Pitch	5.2 mm

Marking

Number of individual labels	120
Number of individual labels per row	12
Number of marker strips	10
Slot type	flat

Dimensions

Width	4.55 mm
Height	8.12 mm
Depth	2.00 mm
Pitch	5.2 mm

Material specifications

Color	orange (RAL 2003)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

ZBFM 5/OG:UNBEDRUCKT - Flat zack marker sheet



0807180

<https://www.phoenixcontact.com/us/products/0807180>

Classifications

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

0807180

<https://www.phoenixcontact.com/us/products/0807180>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com