

0810892:0014

<https://www.phoenixcontact.com/us/products/0810892:0014>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker pin, labeled with the number: 14, 100 identically printed marker pins per package, white, for terminal block width: 4.2 mm, mounting type: plug in

## Commercial data

Item number	0810892:0014
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG05
Product key	BG212B
GTIN	4017918864262
Weight per piece (including packing)	0.045 g
Weight per piece (excluding packing)	0.045 g
Customs tariff number	49119900
Country of origin	PL

0810892:0014

<https://www.phoenixcontact.com/us/products/0810892:0014>

## Technical data

### Product properties

Product type	Labeled terminal marker
Pitch	4.2 mm

### Marking

Printing	14
----------	----

### Mounting

Mounting type	plug in
---------------	---------

### Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

### Dimensions

Width	4 mm
Height	4 mm
Pitch	4.2 mm

#### Text field

Text field width	4.00 mm
Text field height	4.00 mm

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

0810892:0014

<https://www.phoenixcontact.com/us/products/0810892:0014>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

0810892:0014

<https://www.phoenixcontact.com/us/products/0810892:0014>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)