

GPA 610X610X0,8... - Engraving plate for outdoor use



0811406

<https://www.phoenixcontact.com/us/products/0811406>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Engraving plate for outdoor use, material thickness: 0.8 mm, length: 610 mm, width: 610 mm, engraving plate



Commercial data

Item number	0811406
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	BG2415
GTIN	4017918906474
Weight per piece (including packing)	370 g
Weight per piece (excluding packing)	370 g
Customs tariff number	39205100
Country of origin	DE

Technical data

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	1
Identification technology	Engraving

Dimensions

Width	610.00 mm
Height	610.00 mm
Depth	0.70 mm

Text field

Text field width	610 mm
Text field height	610 mm

Material specifications

Color	silver-colored
Material	ABS
Base element material	ABS

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 85 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
---------------	-------------------------------------

Mounting

Mounting type	screw, rivet
---------------	--------------

0811406

<https://www.phoenixcontact.com/us/products/0811406>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

GPA 610X610X0,8... - Engraving plate for outdoor use



0811406

<https://www.phoenixcontact.com/us/products/0811406>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com