


# ZB 6/YE:UNPRINTED - Zack marker strip



0812722

<https://www.phoenixcontact.com/us/products/0812722>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, yellow (RAL 1018), unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snap in, for terminal block width: 6.2 mm, Number of individual labels: 10

## Commercial data

Item number	0812722
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG05
Product key	BG2112
GTIN	4017918966249
Weight per piece (including packing)	1.56 g
Weight per piece (excluding packing)	1.273 g
Customs tariff number	39269097
Country of origin	DE

## Technical data

### Product properties

Product type	Terminal marker
Pitch	6.2 mm

### Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10
Slot type	high

### Dimensions

Width	6.15 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	6.2 mm

### Material specifications

Color	yellow (RAL 1018)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	snap in
---------------	---------

# ZB 6/YE:UNPRINTED - Zack marker strip



0812722

<https://www.phoenixcontact.com/us/products/0812722>

## Classifications

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# ZB 6/YE:UNPRINTED - Zack marker strip



0812722

<https://www.phoenixcontact.com/us/products/0812722>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)