

# ZBU SO:USA PNL/LP DOM MOD 4-5 - Zack marker strip

0814872

<https://www.phoenixcontact.com/us/products/0814872>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, white (RAL 9010), for terminal block width: 6.2 mm

## Commercial data

Item number	0814872
Packing unit	100 pc
Minimum order quantity	1 pc
Sales key	BG24
Product key	BG8112
GTIN	4046356014083
Weight per piece (including packing)	3.5 g
Weight per piece (excluding packing)	3.5 g
Customs tariff number	49119900
Country of origin	DE

# ZBU SO:USA PNL/LP DOM MOD 4-5 - Zack marker strip



0814872

<https://www.phoenixcontact.com/us/products/0814872>

## Technical data

### Product properties

Product type	Terminal marker
Pitch	6.2 mm

### Marking

Slot type	high
-----------	------

### Dimensions

Width	6.15 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	6.2 mm

### Material specifications

Color	white (RAL 9010)
-------	------------------

### Environmental and real-life conditions

#### Ambient conditions

Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

# ZBU SO:USA PNL/LP DOM MOD 4-5 - Zack marker strip



0814872

<https://www.phoenixcontact.com/us/products/0814872>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131505
-------------	----------

# ZBU SO:USA PNL/LP DOM MOD 4-5 - Zack marker strip



0814872

<https://www.phoenixcontact.com/us/products/0814872>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)