

BNB WH:GLEICHE ZAHLEN 6 - Zack marker strip



0810892:0006

<https://www.phoenixcontact.com/us/products/0810892:0006>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker pin, labeled with the number: 6, 100 identically printed marker pins per package, white, for terminal block width: 4.2 mm, mounting type: plug in

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0810892:0006 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BG05 |
| Product key | BG212B |
| GTIN | 4017918864187 |
| Weight per piece (including packing) | 0.05 g |
| Weight per piece (excluding packing) | 0.02 g |
| Customs tariff number | 49119900 |
| Country of origin | PL |

0810892:0006

<https://www.phoenixcontact.com/us/products/0810892:0006>

Technical data

Product properties

| | |
|--------------|-------------------------|
| Product type | Labeled terminal marker |
| Pitch | 4.2 mm |

Marking

| | |
|----------|---|
| Printing | 6 |
|----------|---|

Mounting

| | |
|---------------|---------|
| Mounting type | plug in |
|---------------|---------|

Material specifications

| | |
|--|--------------------------------|
| Color | white (RAL 9010) |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Base element material | PA |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Dimensions

| | |
|--------|--------|
| Width | 4 mm |
| Height | 4 mm |
| Pitch | 4.2 mm |

Text field

| | |
|-------------------|---------|
| Text field width | 4.00 mm |
| Text field height | 4.00 mm |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

BNB WH:GLEICHE ZAHLEN 6 - Zack marker strip



0810892:0006

<https://www.phoenixcontact.com/us/products/0810892:0006>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000761 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

BNB WH:GLEICHE ZAHLEN 6 - Zack marker strip



0810892:0006

<https://www.phoenixcontact.com/us/products/0810892:0006>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com