

0810892:0014

<https://www.phoenixcontact.com/us/products/0810892:0014>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker pin, labeled with the number: 14, 100 identically printed marker pins per package, white, for terminal block width: 4.2 mm, mounting type: plug in

Commercial data

Item number	0810892:0014
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG05
Product key	BG212B
GTIN	4017918864262
Weight per piece (including packing)	0.045 g
Weight per piece (excluding packing)	0.045 g
Customs tariff number	49119900
Country of origin	PL

Technical data

Product properties

Product type	Terminal marker
Pitch	4.2 mm

Marking

Printing	14
----------	----

Dimensions

Width	4 mm
Height	4 mm
Pitch	4.2 mm

Text field

Text field width	4.00 mm
Text field height	4.00 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	plug in
---------------	---------

0810892:0014

<https://www.phoenixcontact.com/us/products/0810892:0014>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

0810892:0014

<https://www.phoenixcontact.com/us/products/0810892:0014>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com