

KLM 3 - Terminal strip marker carrier



0811969

<https://www.phoenixcontact.com/us/products/0811969>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminal strip marker carrier, adjustable height, for CLIPFIX 15, CLIPFIX 35, and CLIPFIX 35-5 end brackets, can be marked using labels in 20 x 8 mm format



Your advantages

- The KLM range has been specifically developed for CLIPFIX end brackets
- The precise engagement mechanism enables infinite adjustment of the labeling area height

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0811969 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BG12 |
| Product key | BG211A |
| GTIN | 4017918952891 |
| Weight per piece (including packing) | 0.56 g |
| Weight per piece (excluding packing) | 0.538 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

KLM 3 - Terminal strip marker carrier



0811969

<https://www.phoenixcontact.com/us/products/0811969>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Marker carriers |
|--------------|-----------------|

Dimensions

| | |
|--------|----------|
| Width | 10.00 mm |
| Height | 21.60 mm |
| Depth | 27.32 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 20 mm |
| Text field height | 8 mm |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 |
| Base element material | PA |
| Relative insulation material temperature index (Elec., UL 746 B) | 125 °C |
| Components | halogen-free |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Mounting

| | |
|---------------|---------|
| Mounting type | plug in |
|---------------|---------|

KLM 3 - Terminal strip marker carrier



0811969

<https://www.phoenixcontact.com/us/products/0811969>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
| ECLASS-15.0 | 27281105 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002248 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

KLM 3 - Terminal strip marker carrier



0811969

<https://www.phoenixcontact.com/us/products/0811969>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.003 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com