

# GPA/SK 296X200X0,8 ... - Engraving plate for outdoor use



0814652

<https://www.phoenixcontact.com/us/products/0814652>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Engraving plate for outdoor use, Plate, unmarked, can be labeled with: P1 ENGRAVING UNIT, ENGRAVING UNIT, mounting type: adhesive, text field height: 200 mm, text field width: 296 mm



## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 0814652                        |
| Packing unit                         | 12 pc                          |
| Minimum order quantity               | 12 pc                          |
| Note                                 | Made to order (non-returnable) |
| Product key                          | BG2415                         |
| GTIN                                 | 4017918978471                  |
| Weight per piece (including packing) | 70.4 g                         |
| Weight per piece (excluding packing) | 69 g                           |
| Country of origin                    | DE                             |

# GPA/SK 296X200X0,8 ... - Engraving plate for outdoor use



0814652

<https://www.phoenixcontact.com/us/products/0814652>

## Technical data

### Product properties

|              |               |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

### Marking

|                           |           |
|---------------------------|-----------|
| Identification technology | Engraving |
|---------------------------|-----------|

### Dimensions

|        |        |
|--------|--------|
| Width  | 296 mm |
| Height | 200 mm |
| Depth  | 0.8 mm |

### Text field

|                   |        |
|-------------------|--------|
| Text field width  | 296 mm |
| Text field height | 200 mm |

### Material specifications

|                       |                                   |
|-----------------------|-----------------------------------|
| Color                 | according to customer requirement |
| Base element material | ABS                               |

### Environmental and real-life conditions

#### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)                     | -20 °C ... 85 °C  |
| Recommended ambient temperature (storage/transport) | 23 °C   |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
|---------------|--------------------------------|

#### Wipe resistance of inscriptions

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
|---------------|-------------------------------------|

### Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# GPA/SK 296X200X0,8 ... - Engraving plate for outdoor use



0814652

<https://www.phoenixcontact.com/us/products/0814652>

## Classifications

### ECLASS

ECLASS-13.0

27281103

### ETIM

ETIM 9.0

EC001288

### UNSPSC

UNSPSC 21.0

39131500

# GPA/SK 296X200X0,8 ... - Engraving plate for outdoor use



0814652

<https://www.phoenixcontact.com/us/products/0814652>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)