

ZBU SO:USA 15 POS OF L - Marker for terminal blocks

0820264

<https://www.phoenixcontact.com/us/products/0820264>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for terminal blocks, for terminal block width: 8.2 mm

Commercial data

Item number	0820264
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG24
Product key	BG8112
GTIN	4046356279901
Weight per piece (including packing)	11.1 g
Weight per piece (excluding packing)	11.1 g
Customs tariff number	49119900
Country of origin	DE

ZBU SO:USA 15 POS OF L - Marker for terminal blocks



0820264

<https://www.phoenixcontact.com/us/products/0820264>

Technical data

Product properties

Product type	Terminal marker
Pitch	8.2 mm

Marking

Slot type	high
-----------	------

Dimensions

Width	6.15 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	8.2 mm

Material specifications

Color	white (RAL 9010)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

ZBU SO:USA 15 POS OF L - Marker for terminal blocks



0820264

<https://www.phoenixcontact.com/us/products/0820264>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131505
-------------	----------

ZBU SO:USA 15 POS OF L - Marker for terminal blocks



0820264

<https://www.phoenixcontact.com/us/products/0820264>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com