

ES/KLM -GB CUS - Insert strip

0824389

<https://www.phoenixcontact.com/us/products/0824389>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert strip, can be ordered: in sheets, labeled according to customer specifications, mounting type: insert



Figure shows a combination of the KLM and ESL 26 x 6 versions

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0824389 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BG8114 |
| GTIN | 4046356352642 |
| Weight per piece (including packing) | 10 g |
| Weight per piece (excluding packing) | 9 g |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Terminal marker |
|--------------|-----------------|

Marking

| | |
|---------------------------|---------|
| Identification technology | Plotter |
|---------------------------|---------|

Dimensions

| | |
|--------|-------|
| Width | 25 mm |
| Length | 6 mm |

Material specifications

| | |
|------------|--------------------------------|
| Color | white |
| Material | Polyester foil |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|--------|
| Mounting type | insert |
|---------------|--------|

ES/KLM -GB CUS - Insert strip



0824389

<https://www.phoenixcontact.com/us/products/0824389>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com