

ES/LP-BW-GB CUS - Insert strip



0824395

<https://www.phoenixcontact.com/us/products/0824395>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Device marking, can be labeled as per customer specifications



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0824395 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BG8134 |
| GTIN | 4046356352666 |
| Weight per piece (including packing) | 10 g |
| Weight per piece (excluding packing) | 9 g |
| Country of origin | PL |

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Terminal marker |
|--------------|-----------------|

Marking

| | |
|---------------------------|---------|
| Identification technology | Plotter |
|---------------------------|---------|

Dimensions

| | |
|--------|----------|
| Width | 29.50 mm |
| Height | 8.30 mm |
| Depth | 0.20 mm |
| Length | 8 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 29 mm |
| Text field height | 8 mm |

Material specifications

| | |
|-----------------------|--------------------------------|
| Color | white (RAL 9010) |
| Base element material | Polyester |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Wipe resistance of inscriptions

| | |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

Mounting

| | |
|---------------|--------|
| Mounting type | insert |
|---------------|--------|

ES/LP-BW-GB CUS - Insert strip



0824395

<https://www.phoenixcontact.com/us/products/0824395>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281106 |
| ECLASS-15.0 | 27281106 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

ES/LP-BW-GB CUS - Insert strip



0824395

<https://www.phoenixcontact.com/us/products/0824395>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com