

ZBFM 5/OG CUS - Flat zack marker sheet



0825035

<https://www.phoenixcontact.com/us/products/0825035>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the white version

Flat zack marker sheet, can be ordered: by sheet, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 5.2 mm, Number of individual labels: 120

Commercial data

Item number	0825035
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8113
GTIN	4046356357678
Weight per piece (including packing)	5.26 g
Weight per piece (excluding packing)	5.26 g
Country of origin	DE

ZBFM 5/OG CUS - Flat zack marker sheet



0825035

<https://www.phoenixcontact.com/us/products/0825035>

Technical data

Product properties

Product type	Terminal marker
Pitch	5.2 mm

Marking

Number of individual labels	120
Number of individual labels per row	12
Slot type	flat

Dimensions

Width	4.55 mm
Height	8.12 mm
Depth	2.00 mm
Pitch	5.2 mm

Material specifications

Color	orange
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	snap into flat marker groove
---------------	------------------------------

ZBFM 5/OG CUS - Flat zack marker sheet




0825035

<https://www.phoenixcontact.com/us/products/0825035>

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

ZBFM 5/OG CUS - Flat zack marker sheet



0825035

<https://www.phoenixcontact.com/us/products/0825035>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com