

SK 5,0 REEL P12,5 WH CUS - Marker card



0825130

<https://www.phoenixcontact.com/us/products/0825130>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker card, Roll, can be ordered: by card, white (RAL 9010), labeled according to customer specifications, mounting type: adhesive, for terminal block width: 12.5 mm, Number of individual labels: 10

Commercial data

Item number	0825130
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8113
GTIN	4046356355117
Weight per piece (including packing)	1.99 g
Weight per piece (excluding packing)	1.99 g
Country of origin	PL

SK 5,0 REEL P12,5 WH CUS - Marker card



0825130

<https://www.phoenixcontact.com/us/products/0825130>

Technical data

Notes

Order information:	Marking up to max. 25-pos.
--------------------	----------------------------

Product properties

Product type	Terminal marker
Pitch	12.5 mm

Marking

Number of individual labels	10
Number of individual labels per row	1
Number of marker strips	10
Identification technology	Thermal transfer

Dimensions

Width	50.00 mm
Height	5.00 mm
Depth	0.10 mm
Pitch	12.5 mm

Material specifications

Foil strength	53 µm
Adhesive strength	20 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

SK 5,0 REEL P12,5 WH CUS - Marker card



0825130

<https://www.phoenixcontact.com/us/products/0825130>

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Mounting

Mounting type	adhesive
---------------	----------

SK 5,0 REEL P12,5 WH CUS - Marker card


0825130

<https://www.phoenixcontact.com/us/products/0825130>



Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

SK 5,0 REEL P12,5 WH CUS - Marker card



0825130

<https://www.phoenixcontact.com/us/products/0825130>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SK 5,0 REEL P12,5 WH CUS - Marker card



0825130

<https://www.phoenixcontact.com/us/products/0825130>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com