

# SD-WMS 3 (CH) YE:Z - Wire marking tag



0825557:Z

<https://www.phoenixcontact.com/us/products/0825557:Z>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, labeled with the capital letter: Letters, yellow, the dimensions of the replacement product differ from the previous product!, mounting type: thread on

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0825557:Z     |
| Packing unit                         | 200 pc        |
| Minimum order quantity               | 200 pc        |
| Product key                          | BG222B        |
| GTIN                                 | 4046356415408 |
| Weight per piece (including packing) | 0.033 MGM     |
| Weight per piece (excluding packing) | 0.033 MGM     |
| Country of origin                    | SE            |

## Technical data

### Product properties

|              |                  |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

### Marking

|           |         |
|-----------|---------|
| Printing  | Letters |
| Slot type | Profile |

### Dimensions

|        |         |
|--------|---------|
| Width  | 3.2 mm  |
| Height | 3.6 mm  |
| Length | 3.50 mm |

### External dimensions

|                  |                 |
|------------------|-----------------|
| Outside diameter | 1.3 mm ... 3 mm |
|------------------|-----------------|

### Material specifications

|  |                                |
|--|--------------------------------|
| Color                                  | yellow                         |
| Material                               | Polyvinyl chloride             |
| Flammability rating according to UL 94 | V0                             |
| Components                             | Free from silicone and cadmium |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -30 °C ... 60 °C |
|---------------------------------|------------------|

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Mounting

|               |           |
|---------------|-----------|
| Mounting type | thread on |
|---------------|-----------|

# SD-WMS 3 (CH) YE:Z - Wire marking tag



0825557:Z

<https://www.phoenixcontact.com/us/products/0825557:Z>

## Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)