

SD-WMS 3 (CH)R YE:R - Wire marking tag



0825667:R

<https://www.phoenixcontact.com/us/products/0825667:R>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Wire marking tag, labeled with the capital letter: R, yellow, mounting type: thread on



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0825667:R |
| Packing unit | 500 pc |
| Minimum order quantity | 500 pc |
| Product key | BG2221 |
| GTIN | 4046356419611 |
| Weight per piece (including packing) | 0.06 g |
| Weight per piece (excluding packing) | 0.028 g |
| Country of origin | SE |

SD-WMS 3 (CH)R YE:R - Wire marking tag



0825667:R

<https://www.phoenixcontact.com/us/products/0825667:R>

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

Marking

| | |
|-----------|---------|
| Printing | R |
| Slot type | Profile |

Dimensions

| | |
|--------|---------|
| Width | 3.2 mm |
| Height | 3.6 mm |
| Length | 3.50 mm |

External dimensions

| | |
|------------------|-----------------|
| Outside diameter | 1.3 mm ... 3 mm |
|------------------|-----------------|

Material specifications

| | |
|--|--------------------------------|
| Color | yellow (RAL 1018) |
| Material | Polyvinyl chloride |
| Flammability rating according to UL 94 | V0 |
| Base element material | PVC |
| Components | Free from silicone and cadmium |

Cable/line

| | |
|-------------------------|-----------------|
| External cable diameter | 1.3 mm ... 3 mm |
|-------------------------|-----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -30 °C ... 60 °C |
|---------------------------------|------------------|

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|-----------|
| Mounting type | thread on |
|---------------|-----------|

SD-WMS 3 (CH)R YE:R - Wire marking tag



0825667:R

<https://www.phoenixcontact.com/us/products/0825667:R>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001530 |
|-----------|----------|

SD-WMS 3 (CH)R YE:R - Wire marking tag



0825667:R

<https://www.phoenixcontact.com/us/products/0825667:R>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com