

SD-WMS 5 (NU)S CC:6 - Wire marking tag



0826116:6

<https://www.phoenixcontact.com/us/products/0826116:6>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, labeled with the number: Numbers, white, mounting type: thread on

The figure shows the version SD-WMS 5 (NU)S
YE

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 0826116:6 |
| Packing unit | 250 pc |
| Minimum order quantity | 1 pc |
| Product key | BG2222 |
| GTIN | 4046356423786 |
| Weight per piece (including packing) | 0.09 g |
| Weight per piece (excluding packing) | 0.09 g |
| Country of origin | SE |

SD-WMS 5 (NU)S CC:6 - Wire marking tag



0826116:6

<https://www.phoenixcontact.com/us/products/0826116:6>

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

Marking

| | |
|-----------|---------|
| Printing | Numbers |
| Slot type | Profile |

Dimensions

| | |
|--------|---------|
| Width | 3.2 mm |
| Height | 5.5 mm |
| Length | 4.20 mm |

External dimensions

| | |
|------------------|-----------------|
| Outside diameter | 2.5 mm ... 5 mm |
|------------------|-----------------|

Material specifications

| | |
|----------|--------------------|
| Color | white |
| Material | Polyvinyl chloride |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|-----------|
| Mounting type | thread on |
|---------------|-----------|

SD-WMS 5 (NU)S CC:6 - Wire marking tag



0826116:6

<https://www.phoenixcontact.com/us/products/0826116:6>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com