

# SD-WMS 16 (CH) YE:R - Wire marking tag



0826365:R

<https://www.phoenixcontact.com/us/products/0826365:R>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, labeled with the capital letter: R, lettering field size: 6.2 x 4 mm, yellow, mounting type: thread on

The figure shows the article SD-WMS 10 (CH) YE

## Commercial data

Item number	0826365:R
Packing unit	20 pc
Minimum order quantity	20 pc
Product key	BG2221
GTIN	4046356426107
Weight per piece (including packing)	0.95 g
Weight per piece (excluding packing)	0.95 g
Country of origin	SE

# SD-WMS 16 (CH) YE:R - Wire marking tag



0826365:R

<https://www.phoenixcontact.com/us/products/0826365:R>

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Marking

Printing	R
Slot type	Profile

### Dimensions

Width	6.2 mm
Height	16.5 mm
Length	11.00 mm

### External dimensions

Outside diameter	8 mm ... 16 mm
------------------	----------------

### Material specifications

Color	yellow (RAL 1018)
Material	Polyvinyl chloride
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Free from silicone and cadmium

### Cable/line

External cable diameter	8 mm ... 16 mm
-------------------------	----------------

### Mounting

Mounting type	thread on
---------------	-----------

# SD-WMS 16 (CH) YE:R - Wire marking tag



0826365:R

<https://www.phoenixcontact.com/us/products/0826365:R>

## Classifications

### ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

### ETIM

ETIM 10.0	EC001530
-----------	----------

# SD-WMS 16 (CH) YE:R - Wire marking tag



0826365:R

<https://www.phoenixcontact.com/us/products/0826365:R>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)