

SD-WMS 16 (SY) YE:- - Wire marking tag

0826378:-

<https://www.phoenixcontact.com/us/products/0826378:->

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Wire marking tag, labeled with the symbol: -, lettering field size: 6.2 x 4 mm, yellow, mounting type: thread on

The figure shows the article SD-WMS 10 (CH) YE

Commercial data

Item number	0826378:-
Packing unit	20 pc
Minimum order quantity	20 pc
Product key	BG2221
GTIN	4046356426206
Weight per piece (including packing)	0.782 g
Weight per piece (excluding packing)	0.782 g
Country of origin	SE

SD-WMS 16 (SY) YE:- - Wire marking tag



0826378:-

<https://www.phoenixcontact.com/us/products/0826378:->

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Printing	-
Slot type	Profile

Dimensions

Width	6.2 mm
Height	16.5 mm
Length	11.00 mm

External dimensions

Outside diameter	8 mm ... 16 mm
------------------	----------------

Material specifications

Color	yellow (RAL 1018)
Material	Polyvinyl chloride
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Free from silicone and cadmium

Cable/line

External cable diameter	8 mm ... 16 mm
-------------------------	----------------

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	thread on
---------------	-----------

SD-WMS 16 (SY) YE:- - Wire marking tag



0826378:-

<https://www.phoenixcontact.com/us/products/0826378:->

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530
-----------	----------

SD-WMS 16 (SY) YE:- - Wire marking tag



0826378:-

<https://www.phoenixcontact.com/us/products/0826378:->

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com