

# SD-WMTBS (NU) VA:5 - Marking material



0826556:5

<https://www.phoenixcontact.com/us/products/0826556:5>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marking collar, labeled with the number: Numbers, silver-colored, mounting type: slide-on

The figure shows a version of the article

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 0826556:5     |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BG17          |
| Product key                          | BG2322        |
| GTIN                                 | 4046356414036 |
| Weight per piece (including packing) | 0.201 g       |
| Weight per piece (excluding packing) | 0.199 g       |
| Customs tariff number                | 83100000      |
| Country of origin                    | SE            |

# SD-WMTBS (NU) VA:5 - Marking material



0826556:5

<https://www.phoenixcontact.com/us/products/0826556:5>

## Technical data

### Product properties

|              |                  |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

### Marking

|          |         |
|----------|---------|
| Printing | Numbers |
|----------|---------|

### Dimensions

|        |          |
|--------|----------|
| Width  | 5.5 mm   |
| Length | 10.90 mm |

### External dimensions

|                  |                  |
|------------------|------------------|
| Outside diameter | 16 mm ... 305 mm |
|------------------|------------------|

### Text field

|                   |         |
|-------------------|---------|
| Text field width  | 5.50 mm |
| Text field height | 4.00 mm |

### Material specifications

|                       |                 |
|-----------------------|-----------------|
| Color                 | silver-colored  |
| Material              | Stainless steel |
| Base element material | Stainless steel |

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Mounting

|               |          |
|---------------|----------|
| Mounting type | slide-on |
|---------------|----------|

# SD-WMTBS (NU) VA:5 - Marking material



0826556:5

<https://www.phoenixcontact.com/us/products/0826556:5>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001530 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

# SD-WMTBS (NU) VA:5 - Marking material



0826556:5

<https://www.phoenixcontact.com/us/products/0826556:5>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)