

UCT-TMF 12 VT CUS - Marker for terminal blocks



0829690

<https://www.phoenixcontact.com/us/products/0829690>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marker for terminal blocks, can be ordered: by sheet, violet (RAL 4005), labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 12 mm, Number of individual labels: 30



Your advantages

- The UCT-TM... UniCard labeling range includes markers for Phoenix Contact products with tall and flat marker grooves, e.g. terminals
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

Commercial data

Item number	0829690
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8118
GTIN	4046356598439
Weight per piece (including packing)	11.599 g
Weight per piece (excluding packing)	9.1 g
Country of origin	PL

Technical data

Product properties

Product type	Terminal marker
Pitch	12 mm

Marking

Number of individual labels	30
Number of individual labels per row	5
Slot type	flat
Identification technology	Thermotransfer

Dimensions

Width	11.45 mm
Height	6.30 mm
Depth	1.64 mm
Pitch	12 mm
Length	5 mm

Material specifications

RoHS compliant	yes
Color	violet (RAL 4005)
Flammability rating according to UL 94	V0
Base element material	PC
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Standards and regulations

UCT-TMF 12 VT CUS - Marker for terminal blocks



0829690

<https://www.phoenixcontact.com/us/products/0829690>

Wipe resistance

DIN EN 61010-1 (VDE 0411-1)

Mounting

Mounting type

snap into flat marker groove

UCT-TMF 12 VT CUS - Marker for terminal blocks



0829690

<https://www.phoenixcontact.com/us/products/0829690>

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

UCT-TMF 12 VT CUS - Marker for terminal blocks



0829690

<https://www.phoenixcontact.com/us/products/0829690>

Classifications

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UCT-TMF 12 VT CUS - Marker for terminal blocks



0829690

<https://www.phoenixcontact.com/us/products/0829690>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com