


# PABA YE/18 - Cable marker



0829428

<https://www.phoenixcontact.com/us/products/0829428>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Strip, yellow (RAL 1018), unmarked, can be labeled with: CMS-P1-PLOTTER, cable diameter range: 0.6 ... 22 mm, mounting type: slide-on, text field height: 4 mm, text field width: 18 mm

## Commercial data

Item number	0829428
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	BG2213
GTIN	4046356559225
Weight per piece (including packing)	6.21 g
Weight per piece (excluding packing)	4.5 g
Country of origin	CN

## Technical data

### Product properties

Product type	Conductor marker
--------------	------------------

### Dimensions

Width	18 mm
Length	4 mm

### Text field

Text field width	18 mm
Text field height	4 mm

### Material specifications

Color	yellow (RAL 1018)
-------	-------------------

### Cable/line

External cable diameter	0.6 mm ... 22 mm
-------------------------	------------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-15 °C ... 65 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

### Mounting

Mounting type	slide-on
---------------	----------

# PABA YE/18 - Cable marker

0829428

<https://www.phoenixcontact.com/us/products/0829428>



## Classifications

### ECLASS

ECLASS-13.0

27281103

### ETIM

ETIM 9.0

EC001288

### UNSPSC

UNSPSC 21.0

39131500

# PABA YE/18 - Cable marker



0829428

<https://www.phoenixcontact.com/us/products/0829428>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)