

# WM-CARRIER/B (55X15)LPR - Cable marker carrier



0830424

<https://www.phoenixcontact.com/us/products/0830424>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker carrier, unmarked, mounting type: Assembly with cable ties, cable diameter:  $\geq 9$  mm, text field height: 15 mm, text field width: 55 mm

## Commercial data

Item number	0830424
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG12
Product key	BG231A
GTIN	4046356716147
Weight per piece (including packing)	0.876 g
Weight per piece (excluding packing)	0.876 g
Customs tariff number	39204910
Country of origin	DK

## Technical data

### Product properties

Product type	Marker carriers
--------------	-----------------

### Dimensions

Width	100 mm
Height	15 mm
Depth	0.36 mm

### Text field

Text field width	55 mm
Text field height	15 mm

### Material specifications

Color	transparent
Material	Polyester
Base element material	Polyester
Components	halogen-free

### Cable/line

External cable diameter	≥ 9.00 mm
-------------------------	-----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

# WM-CARRIER/B (55X15)LPR - Cable marker carrier



0830424

<https://www.phoenixcontact.com/us/products/0830424>

## Classifications

### ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

### ETIM

ETIM 10.0	EC002248
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# WM-CARRIER/B (55X15)LPR - Cable marker carrier



0830424

<https://www.phoenixcontact.com/us/products/0830424>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)