

# PMT (10X38) GY - Insert label



0831092

<https://www.phoenixcontact.com/us/products/0831092>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Marking label for conveyed fluids, for equipping CARRIER-PMP (110x38), CARRIER/L-PMP (110x38), and CARRIER-PMP-ENCLOSED (110x38) according to DIN 2403



## Commercial data

Item number	0831092
Packing unit	100 pc
Minimum order quantity	100 pc
Product key	BG261Z
GTIN	4046356941259
Weight per piece (including packing)	0.624 g
Weight per piece (excluding packing)	0.62 g
Country of origin	DE

# PMT (10X38) GY - Insert label



0831092

<https://www.phoenixcontact.com/us/products/0831092>

## Technical data

### Product properties

Product type	Plant marker
Area of application	Identification of flow substances according to DIN 2403

### Marking

Number of individual labels	1
Number of individual labels per row	1

### Dimensions

Width	38.00 mm
Height	10.00 mm
Depth	1.00 mm

### Material specifications

Color	gray (RAL 7042)
Base element material	PVC
Components	Free from silicone and cadmium

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	10 °C
Recommended humidity (storage/transport)	40 % ... 70 % (Storage in a dry and dark place in the original packaging is recommended)

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

### Mounting

Mounting type	latching
---------------	----------

# PMT (10X38) GY - Insert label



0831092

<https://www.phoenixcontact.com/us/products/0831092>

## Classifications

### ECLASS

ECLASS-13.0	27281104
ECLASS-15.0	27281104

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# PMT (10X38) GY - Insert label



0831092

<https://www.phoenixcontact.com/us/products/0831092>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)