

# CARRIER-TMH 300 - Marker carriers



0830670

<https://www.phoenixcontact.com/us/products/0830670>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



**Marker adapter**, 300 mm in length, for manual cutting, can be engaged in flat marker groove, the marking area is rotated by 90°, for UC-TM ...; UCT-TM ...

## Your advantages

- For accommodating ZB ..., UC-TM ... or UCT-TM ... terminal markers which increases the labeling area
- Can be snapped into all terminal blocks in the CLIPLINE complete system that have a flat lateral marker groove

## Commercial data

Item number	0830670
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BG12
Product key	BG211A
GTIN	4046356719186
Weight per piece (including packing)	9.676 g
Weight per piece (excluding packing)	9.676 g
Customs tariff number	39269097
Country of origin	DE

# CARRIER-TMH 300 - Marker carriers



0830670

<https://www.phoenixcontact.com/us/products/0830670>

## Technical data

### Product properties

Product type	Marker carriers
--------------	-----------------

### Dimensions

Width	300.00 mm
Height	8.73 mm
Depth	12.49 mm

### Text field

Text field width	300 mm
Text field height	10.5 mm

### Material specifications

Color	gray (RAL 7042)
Base element material	PA
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

### Mounting

Mounting type	latching
---------------	----------

# CARRIER-TMH 300 - Marker carriers



0830670

<https://www.phoenixcontact.com/us/products/0830670>

## Classifications

### ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

### ETIM

ETIM 10.0	EC002248
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CARRIER-TMH 300 - Marker carriers



0830670

<https://www.phoenixcontact.com/us/products/0830670>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)