

PMST (10X38) BU - Insert label



0831084

<https://www.phoenixcontact.com/us/products/0831084>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Identification label for flow-through substances with centered hole for addition fixing with a pop rivet, for assembling the CARRIER-PMP (110x38), CARRIER/L-PMP (110x38) and CARRIER-PMP-ENCLOSED (110x38) according to DIN 2403



Commercial data

Item number	0831084
Packing unit	100 pc
Minimum order quantity	100 pc
Product key	BG261Z
GTIN	4046356941174
Weight per piece (including packing)	0.585 g
Weight per piece (excluding packing)	0.585 g
Country of origin	DE

PMST (10X38) BU - Insert label



0831084

<https://www.phoenixcontact.com/us/products/0831084>

Technical data

Product properties

Product type	Plant marker
Area of application	Identification of flow substances according to DIN 2403

Marking

Number of individual labels	1
Number of individual labels per row	1

Dimensions

Width	38.00 mm
Height	10.00 mm
Depth	1.00 mm

Material specifications

Color	blue (RAL 5015)
Material	PVC
Flammability rating according to UL 94	V0
Components	Free from silicone and cadmium

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended ambient temperature (storage/transport)	10 °C
Recommended humidity (storage/transport)	40 %

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	latching
---------------	----------

PMST (10X38) BU - Insert label



0831084

<https://www.phoenixcontact.com/us/products/0831084>

Classifications

ECLASS

ECLASS-13.0

27281104

ETIM

ETIM 9.0

EC001288

UNSPSC

UNSPSC 21.0

39131500

PMST (10X38) BU - Insert label



0831084

<https://www.phoenixcontact.com/us/products/0831084>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com