

AE MP SH EP 250X255 - Mounting panel



0899440

<https://www.phoenixcontact.com/us/products/0899440>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting panel, width: 235 mm, height: 239 mm, color: silver-colored



The figure shows a similar product

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 0899440 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | NULL |
| Product key | BH9Z4X |
| GTIN | 4055626281285 |
| Weight per piece (including packing) | 9.99 g |
| Weight per piece (excluding packing) | 9.99 g |
| Customs tariff number | 94039910 |
| Country of origin | DE |

AE MP SH EP 250X255 - Mounting panel



0899440

<https://www.phoenixcontact.com/us/products/0899440>

Technical data

Product properties

| | |
|--------------|----------------|
| Product type | Mounting plate |
|--------------|----------------|

Dimensions

| | |
|--------------------------------------|--------|
| Width | 235 mm |
| Height | 239 mm |
| Hole diameter | 7 mm |
| Material thickness of mounting panel | 2 mm |

Material specifications

| | |
|----------|-------------------|
| Color | silver-colored |
| Material | Steel, galvanized |
| Coating | zinc plating |

AE MP SH EP 250X255 - Mounting panel



0899440

<https://www.phoenixcontact.com/us/products/0899440>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27182811 |
| ECLASS-15.0 | 27182811 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002620 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

AE MP SH EP 250X255 - Mounting panel



0899440

<https://www.phoenixcontact.com/us/products/0899440>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com