

NBC-M12MRD/0,72-93E CV - Network cable



1003406

<https://www.phoenixcontact.com/us/products/1003406>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet CAT5, 4-position, shielded, Plug straight M12, on free cable end, cable length: 0.71 m, Customer version

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 1003406 |
| Packing unit | 1 pc |
| Minimum order quantity | 50 pc |
| Note | Made to order (non-returnable) |
| Product key | AF1CJI |
| GTIN | 4055626476346 |
| Weight per piece (including packing) | 45.5 g |
| Weight per piece (excluding packing) | 45.5 g |
| Country of origin | PL |

1003406

<https://www.phoenixcontact.com/us/products/1003406>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable preassembled |
| Number of positions | 4 |

Interfaces

| | |
|----------------------|---------------|
| Signal type/category | Ethernet CAT5 |
|----------------------|---------------|

Electrical properties

| | |
|-----------------------|---------|
| Nominal voltage U_N | 48 V AC |
| | 60 V DC |

Connector

Connection 1

| | |
|---------------------|-------------------|
| Type | Plug straight M12 |
| Number of positions | 4 |

Connection 2

| | |
|------|----------------|
| Type | free cable end |
|------|----------------|

Cable/line

| | |
|----------------------|---------------|
| Cable length | 0.71 m |
| Signal type/category | Ethernet CAT5 |

NBC-M12MRD/0,72-93E CV - Network cable



1003406

<https://www.phoenixcontact.com/us/products/1003406>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

NBC-M12MRD/0,72-93E CV - Network cable



1003406

<https://www.phoenixcontact.com/us/products/1003406>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com