

# KLM - Terminal strip marker carrier



1004306

<https://www.phoenixcontact.com/us/products/1004306>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Terminal strip marker carrier, for E/UK or CLIPFIX 35 end brackets, can be marked using insert labels in 25 x 6 mm format



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1004306       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Sales key                            | BG12          |
| Product key                          | BG211A        |
| GTIN                                 | 4017918012007 |
| Weight per piece (including packing) | 1.09 g        |
| Weight per piece (excluding packing) | 1.1 g         |
| Customs tariff number                | 39269097      |
| Country of origin                    | DE            |

# KLM - Terminal strip marker carrier



1004306

<https://www.phoenixcontact.com/us/products/1004306>

## Technical data

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Marker carriers |
|--------------|-----------------|

### Dimensions

|        |          |
|--------|----------|
| Width  | 8.00 mm  |
| Height | 28.00 mm |
| Depth  | 22.00 mm |

### Text field

|                   |       |
|-------------------|-------|
| Text field width  | 25 mm |
| Text field height | 6 mm  |

### Material specifications

|  |                                |
|--|--------------------------------|
| Color                                  | transparent                    |
| Flammability rating according to UL 94 | HB                             |
| Base element material                  | ABS                            |
| Components                             | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|   |                  |
|---|------------------|
| Ambient temperature (operation)                     | -40 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 23 °C            |
| Recommended humidity (storage/transport)            | 50 %             |

### Mounting

|               |         |
|---------------|---------|
| Mounting type | plug in |
|---------------|---------|

# KLM - Terminal strip marker carrier

1004306

<https://www.phoenixcontact.com/us/products/1004306>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
| ECLASS-15.0 | 27281105 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002248 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# KLM - Terminal strip marker carrier



1004306

<https://www.phoenixcontact.com/us/products/1004306>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)