

WS 5-15 - Warning label

1004445

<https://www.phoenixcontact.com/us/products/1004445>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Warning label, Plate, orange (RAL 2003), labeled: Lightning flash and warning in English, mounting type: plug in, for terminal block width: 15 mm, Number of individual labels: 1



Your advantages

- The warning labels are secured in the bridge shafts of the UK ... modular terminal blocks using plastic screws
- Mains terminal blocks are reliably covered and marked using warning labels
- Accidental actuation of the terminal points is therefore prevented

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1004445 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG20 |
| Product key | BG2511 |
| GTIN | 4017918012113 |
| Weight per piece (including packing) | 6.25 g |
| Weight per piece (excluding packing) | 5.59 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

Technical data

Product properties

| | |
|---------------------|--------------|
| Product type | Plant marker |
| Type | Rectangle |
| Number of positions | 5 |
| Pitch | 15 mm |

Marking

| | |
|-----------------------------|--|
| Number of individual labels | 1 |
| Printing | Lightning flash and warning in English |

Dimensions

| | |
|--------|----------|
| Width | 76.00 mm |
| Height | 37.00 mm |
| Depth | 28.60 mm |
| Pitch | 15 mm |

Material specifications

| | |
|-----------------------|-------------------|
| Color | orange (RAL 2003) |
| Material | PVC |
| Base element material | PVC |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -15 °C ... 65 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|---------|
| Mounting type | plug in |
|---------------|---------|

WS 5-15 - Warning label



1004445

<https://www.phoenixcontact.com/us/products/1004445>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281107 |
| ECLASS-15.0 | 27281107 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001777 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 55121700 |
|-------------|----------|

WS 5-15 - Warning label



1004445

<https://www.phoenixcontact.com/us/products/1004445>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com