

PKB 370X4,8 - Cable tie

1005509

<https://www.phoenixcontact.com/us/products/1005509>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable tie, dimensions: L x W, 370 x 4.8 mm, color: transparent



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1005509 |
| Packing unit | 1,000 pc |
| Sales key | BE07 |
| Product key | BE7131 |
| GTIN | 4017918012571 |
| Weight per piece (including packing) | 2.553 g |
| Weight per piece (excluding packing) | 2.42 g |
| Customs tariff number | 39269097 |
| Country of origin | SG |

PKB 370X4,8 - Cable tie



1005509

<https://www.phoenixcontact.com/us/products/1005509>

Technical data

Product properties

| | |
|----------------------|-----------|
| Product type | Cable tie |
| Tensile strength GRP | 220 N |

Dimensions

| | |
|--------|--------|
| Width | 4.8 mm |
| Length | 370 mm |

Material specifications

| | |
|--|--------------|
| Color | transparent |
| Material | PA |
| Flammability rating according to UL 94 | V2 |
| Components | halogen-free |

Cable/line

| | |
|------------------|-------|
| Tensile strength | 220 N |
|------------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (assembly) | -10 °C ... 60 °C |
| Resistance to UV radiation | yes |

Mounting

| | |
|---------------|-------------------|
| Mounting type | Cannot be removed |
|---------------|-------------------|

PKB 370X4,8 - Cable tie



1005509

<https://www.phoenixcontact.com/us/products/1005509>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com