

# PATO 1/23 - Conductor marker carrier



1013892

<https://www.phoenixcontact.com/us/products/1013892>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker carrier, unmarked, cable diameter range: 2 ... 3.5 mm, mounting type: clip on, text field height: 4 mm, text field width: 23 mm

## Your advantages

- Can be labeled using UC-WMT ... or US-WMT ... plastic labels or the EMT ... insert strips
- These marking collars are used for subsequent labeling of systems that have already been wired

## Commercial data

Item number	1013892
Packing unit	500 pc
Minimum order quantity	500 pc
Sales key	BG12
Product key	BG221A
GTIN	4017918014087
Weight per piece (including packing)	0.52 g
Weight per piece (excluding packing)	0.49 g
Customs tariff number	39269097
Country of origin	DE

1013892

<https://www.phoenixcontact.com/us/products/1013892>

## Technical data

### Product properties

Product type	Marker carriers
--------------	-----------------

### Dimensions

Width	23 mm
Height	5.6 mm
Depth	8.2 mm

### Text field

Text field width	23 mm
Text field height	4 mm

### Material specifications

Color	transparent
Material	PVC
Flammability rating according to UL 94	V0
Base element material	PVC
Components	Silicone-free

### Cable/line

External cable diameter	2 mm ... 3.5 mm
-------------------------	-----------------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

### Mounting

Mounting type	clip on
---------------	---------

# PATO 1/23 - Conductor marker carrier



1013892

<https://www.phoenixcontact.com/us/products/1013892>

## Classifications

### ECLASS

ECLASS-13.0	27281105
ECLASS-15.0	27281105

### ETIM

ETIM 10.0	EC002248
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# PATO 1/23 - Conductor marker carrier



1013892

<https://www.phoenixcontact.com/us/products/1013892>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.003 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)