

SACC-DSI-M12MS-8P-M16/1,25AEH - Device connector rear mounting



1013439

<https://www.phoenixcontact.com/us/products/1013439>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, Pin, straight, M12, A-coding, on free cable end, Individual wires, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1238014

Commercial data

Item number	1013439
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	ABQCGB
GTIN	4055626492315
Weight per piece (including packing)	49.5 g
Weight per piece (excluding packing)	45.822 g
Country of origin	DE

SACC-DSI-M12MS-8P-M16/1,25AEH - Device connector rear mounting



1013439

<https://www.phoenixcontact.com/us/products/1013439>

Technical data

Notes

Order information:	Lock nut is included in the scope of delivery
--------------------	---

Product properties

Product type	Circular connectors (device side)
Coding	A
Thread type	M12

Connection data

Conductor connection

Connection method	Individual wires
Contact connection type	Pin

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Connector

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	A

Connection 2

Head design	free cable end
-------------	----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (When plugged in)
	IP65 (When plugged in)
	IP65/IP67

SACC-DSI-M12MS-8P-M16/1,25AEH - Device connector rear mounting



1013439

<https://www.phoenixcontact.com/us/products/1013439>

Classifications

ECLASS

ECLASS-13.0	27440116
-------------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-DSI-M12MS-8P-M16/1,25AEH - Device connector rear mounting



1013439

<https://www.phoenixcontact.com/us/products/1013439>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	7942399a-d462-4518-9708-a1c1bfb56a84

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com