

PML-P102 (D50) - Prohibition sign

1014187

<https://www.phoenixcontact.com/us/products/1014187>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Prohibition sign, Sheet, labeled: Do not connect, mounting type: adhesive, diameter: 50 mm, Number of individual labels: 3

Your advantages

- Stick-on prohibition signs, preprinted with symbol
- Suitable for indoor and outdoor use
- The prohibition signs conform to the ISO 7010 international standard

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1014187 |
| Packing unit | 5 pc |
| Minimum order quantity | 1 pc |
| Product key | BG2624 |
| GTIN | 4046356784825 |
| Weight per piece (including packing) | 5.86 g |
| Weight per piece (excluding packing) | 5.86 g |
| Country of origin | DE |

PML-P102 (D50) - Prohibition sign



1014187

<https://www.phoenixcontact.com/us/products/1014187>

Technical data

Product properties

| | |
|---------------------|---|
| Product type | Plant marker |
| Area of application | Prohibition signs |
| | Prohibition marking according to ISO 7010 |
| Type | circular |

Marking

| | |
|-----------------------------|----------------|
| Number of individual labels | 3 |
| Printing | Do not connect |

Dimensions

| | |
|--------|-------|
| Width | 50 mm |
| Height | 50 mm |

Material specifications

| | |
|------------|---------------|
| Color | red/white |
| Material | PVC |
| Components | Silicone-free |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -40 °C ... 90 °C |
|---------------------------------|------------------|

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

PML-P102 (D50) - Prohibition sign



1014187

<https://www.phoenixcontact.com/us/products/1014187>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com