

PML-T108 (52X560)R CUS - Pipeline marker



1014264

<https://www.phoenixcontact.com/us/products/1014264>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Pipeline marker, can be ordered: by line, Mixed color, labeled according to customer specifications: flammable liquids, mounting type: adhesive, diameter: 0 mm



Your advantages

- Group 8 (combustible liquids)

Commercial data

Item number	1014264
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8151
GTIN	4046356784702
Weight per piece (including packing)	1.99 g
Weight per piece (excluding packing)	1.99 g
Country of origin	PL

PML-T108 (52X560)R CUS - Pipeline marker



1014264

<https://www.phoenixcontact.com/us/products/1014264>

Technical data

Product properties

Product type	Plant marker
Area of application	Pipeline identification according to DIN 2403
Type	Rectangle

Marking

Number of individual labels per row	1
Printing	flammable liquids

Dimensions

Width	560 mm
Height	52 mm
Length	52 mm

Material specifications

RoHS compliant	yes
Foil strength	50 µm
Adhesive	Acrylic
Color	multicolored (RAL -)
	brown (RAL 8028)
	red (RAL 3001)
Material	Polyester

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

PML-T108 (52X560)R CUS - Pipeline marker



1014264

<https://www.phoenixcontact.com/us/products/1014264>

Classifications

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

PML-T108 (52X560)R CUS - Pipeline marker



1014264

<https://www.phoenixcontact.com/us/products/1014264>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com