CRIMPFOX CENTRUS 10S SET - Tool set

1026994

https://www.phoenixcontact.com/us/products/1026994

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cutting, stripping, and crimping set, packaged in a tool case, comprising CUTFOX 18, WIREFOX 10, CRIMPFOX CENTRUS 10S, AI SORTI BOX RD, TOOL-KIT STANDARD EMPTY

Product description

Tool set, equipped

Your advantages

- Universal tools sets with WIREFOX 10, CRIMPFOX-CENTRUS tools from TOOL fox
- Rugged and heavy-duty tool bags
- Ideal for TWIN ferrule

Commercial data

Item number	1026994
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3521
GTIN	4055626520902
Weight per piece (including packing)	1,341.4 g
Weight per piece (excluding packing)	1,324.6 g
Customs tariff number	82060000
Country of origin	SE

Set consists of

CRIMPFOX CENTRUS 10S - Crimping pliers

1213154

https://www.phoenixcontact.com/us/products/1213154



Crimping pliers, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm^2 ... 10 mm^2, also for TWIN ferrules up to 2 x 4 mm^2, automatic cross section adjustment, lateral insertion, equipped with fall protection

AI SORTI BOX RD - Assortment box

3202960

https://www.phoenixcontact.com/us/products/3202960



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

WIREFOX 10 - Stripping tool

1212150

https://www.phoenixcontact.com/us/products/1212150



Stripping tool, for cables and conductors from 0.02 - 10 mm^2, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm^2 stranded/1.5 mm^2 solid, replaceable stripping blade

TOOL-KIT STANDARD EMPTY - Toolbag, unequipped

1212423

https://www.phoenixcontact.com/us/products/1212423



Tool box, unequipped

CUTFOX 18 - Cable-cutting tool

1212129

https://www.phoenixcontact.com/us/products/1212129



Cable cutter, angled, for copper and aluminum up to 18 mm diameter (up to 50 mm^2)

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Tool set
Type of packaging	Bag
Compression	Square crimp

Dimensions

Width	65 mm
Height	315 mm
Length	165 mm

Material specifications

Color	black

Classifications

ECLASS

ECLASS-13.0	21045003
ECLASS-15.0	21045003

ETIM

ETIM 10.0	EC000149

UNSPSC

UNSPSC 21.0	27113200

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	12.769 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com