

# TMC 7 B2 80 46 CA - Wiring bridge



1022235

<https://www.phoenixcontact.com/us/products/1022235>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.




Image shows ...C version

Bus bar for TMC 72... circuit breakers (two phase) 17.8 mm pitch, up to 46 positions. Rated for 80 A (end feed) 600 V AC/DC. UL 508 Listed for connection of UL 1077 rated circuit breakers.

## Commercial data

Item number	1022235
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL09
Product key	CLA126
GTIN	4055626515724
Weight per piece (including packing)	572 g
Weight per piece (excluding packing)	694 g
Customs tariff number	85362010
Country of origin	DE

# TMC 7 B2 80 46 CA - Wiring bridge



1022235

<https://www.phoenixcontact.com/us/products/1022235>

## Technical data

### Product properties

Product type	Bridge
Type	Comb bridge
Number of positions	46

### Electrical properties

Number of phases	2
Nominal voltage $U_N$	600 V AC/DC
Nominal current $I_N$	80 A (End feed)
	160 A (Center feed with two 115 A TMC 7 B2/3TERM PIN terminals required per phase)

### Material specifications

Color	light gray (RAL 7035)
-------	-----------------------

# TMC 7 B2 80 46 CA - Wiring bridge


1022235

<https://www.phoenixcontact.com/us/products/1022235>



## Drawings

Dimensional drawing



# TMC 7 B2 80 46 CA - Wiring bridge



1022235

<https://www.phoenixcontact.com/us/products/1022235>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1022235>



**UL Listed**

Approval ID: E123528



**cUL Listed**

Approval ID: E123528

# TMC 7 B2 80 46 CA - Wiring bridge



1022235

<https://www.phoenixcontact.com/us/products/1022235>

## Classifications

### ECLASS

ECLASS-13.0	27371306
ECLASS-15.0	27371306

### ETIM

ETIM 10.0	EC000215
-----------	----------

### UNSPSC

UNSPSC 21.0	39121600
-------------	----------

# TMC 7 B2 80 46 CA - Wiring bridge



1022235

<https://www.phoenixcontact.com/us/products/1022235>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	4.888 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)